

Photo of Mains Halogens



Photo of Low Voltage Halogens



llogens

Row	Sku	Description			QTY	Facings
Row1	5566	GE 50W SPOT 63 HI-SPOT			12	4
	5439	GE 75W SPOT 95 HI-SPOT			9	3
	5548	GE 100W SPOT 95 HI-SPOT			12	4
Row2	5639	GE HI-SPOT50 SES HALOGEN			12	3
	5567	GE 50W FLD 63 HI-SPOT			6	2
	5592	GE 50W FLOOD 80 HI-SPOT			3	1
	5593	GE 75W FLOOD 80 HI-SPOT			6	2
	5547	GE 75W FLOOD 95 HI-SPOT***			6	2
	5549	GE 100W FLOOD 95 HI-SPOT LAMP			6	2
	5423	SYLVANIA HI-SPOT 120 100W FLD			2	1
Row3	5707	GE HI-SPOT ES50(GU10) 50 DEGREE 10PK			80	4
Row4	5728	GU10 250V 35WATT (38DEG)			36	4
	5649	GE HI-SPOT ES50 (GU10)			42	7
	9826	GU10 240V 50W 5000HR			24	2
	5707	GE HI-SPOT ES50(GU10) 50 DEGREE			36	6
Row5	5670	PHILIPS 50W TWIST N LOCK			60	10
	5695	SYLVANIA HI-SPOT ES63 (GU10)			48	8
Row6	5683	100W 240V 117MM T/HALOGEN LAMP			20	6
	5577	150W K28 240V T/HALOGEN LAMP			20	8
	5338	200W K11 T/HALOGEN LAMP			20	8
	3324	300W K9 240V T/HALOGEN LAMP			20	14
	3325	500W K1 240V T/HALOGEN LAMP			20	8
Row7	5689	60W 240V 78MM T/HALOGEN LAMP			20	1
	5397	100W K14 240V T/HALOGEN LAMP			20	8
	5370	150W K12 240V T/HALOGEN LAMP			20	8
	5322	750W K3 240V T/HALOGEN LAMP			20	2
	5323	1000W K4 T/HALOGEN LAMP			20	2
	5643	G9 240V 25W FROSTED LAMP			20	8
	5731	G9 240V 40W FROSTED LAMP			20	8
	5072	G9 60W FROSTED LAMP			20	8
Row8	2961	40W GLS HALOGEN			10	2
	2990	60W GLS HALOGEN			10	2
	5427	GE 60W BC HALOGENA LAMP			12	2
	5429	GE 100W BC HALOGENA LAMP			12	2
	5428	GE 60W ES HALOGENA LAMP			12	2
	5430	GE 100W ES HALOGENA LAMP			12	2
	5431	GE 150W ES HALOGENA LAMP			12	1
	1719	40W R50 HALOREFLECTOR			6	1
	1720	60W R63 HALOREFLECTOR			6	1
	5529	OSRAM 75W ES HALOLUX (M183C)			4	1
	5356	OSRAM 150W ES HALOLUX (64478)			4	1
	5359	OSRAM 250W ES HALOLUX (64480)			6	2

Row9	8472	GZ10/GU10 SPARE LAMPHOLDER
	7329	GU10 BLUE 50WATT LAMP
	7330	GU10 RED 50WATT LAMP
	7331	GU10 YELLOW 50WATT LAMP
	7332	GU10 GREEN 50WATT LAMP
	5411	JD 100W E14 LAMP
	5405	JD 150 S/E HALOGEN LAMP
	5416	64473KL/M77 75WATT SBC LAMP
	5538	M78 240V 100W SBC LAMP
	5539	M79 240V 150W SBC LAMP

		6	1
		8	2
		8	2
		8	2
		8	2
		6	1
		6	1
		6	1
		6	1
		6	1

Low Voltage Halogens

Number	S/N	Description	QTY	Facings
Row1	5667	5W 12V GU4 12 HALOGEN	4	2
	5480	20W 12V GX5.3 20 HALOGEN M51	4	2
	5482	20W 12V GX5.3 30 HALOGEN M62	4	2
	5484	35W 12V GX5.3 20 HALOGEN M66	4	2
	5457	20W 12V GX5.3 20 HALOGEN M68	4	2
	5459	20W 12V GX5.3 36 HALOGEN M69	4	2
	5461	35W 12V GX5.3 24 HALOGEN M70	4	2
	5462	35W 12V GX5.3 38 HALOGEN M81	4	2
	5464	50W 12V GX5.3 24 HALOGEN M50	4	2
	5415	50W 12V GX5.3 HALOGEN M58	4	2
Row2	5061	20W 12V GU4 36 HALOGEN MR8	8	2
	9724	35w 12v GU4 36 HALOGEN MR8	8	2
	5690	10W 12V GU4 30 HALOGEN	4	1
	5486	20W 12V GX5.3 10 HALOGEN M252	9	3
	5387	20W 12V GU4 20 HALOGEN M251	9	3
	5488	20W 12V GU4 30 HALOGEN M262	9	3
	5489	35W 12V GX5.3 10 HALOGEN M265	9	3
	5490	35W 12V GU4 20 HALOGEN M266	9	3
Row3	5331	50W 12V GX5.3 36 HALOGEN M258	150	5
Row4	5364	20W 12V GX5.3 10 HALOGEN M268	48	6
	5470	20W 12V GX5.3 24 HALOGEN M294	56	7
	5386	20W 12V GX5.3 HALOGEN M269	56	7
Row5	5471	35W 12V GX5.3 12 HALOGEN M271	48	6
	5365	35W 12V GX5.3 24 HALOGEN M270	56	7
	5472	35W 12V GX5.3 38 HALOGEN M281	56	7
Row6	5393	50W 12V GX5.3 10 HALOGEN M249	40	5
	5363	50W 12V GX5.3 24 HALOGEN M250*	40	5
	5331	50W 12V GX5.3 36 HALOGEN M258	40	5
	5473	50W 12V GX5.3 60 HALOGEN M280	40	5
Row7	5496	10W 12V G4 CAPSULE HALOGEN M91	72	6
	5404	20W 12V G4 CAPSULE HALOGEN M47	72	6
	5617	20W 12V GY6.35 CAPSULE HAL M76	72	6

